






PennelCOM
hardware & fastener solutions

UNIT: MM	P/N: 3233-1	COMPONENT: HARDNESS: 52-57 (HRB)
NAME: SLIDE DRAWER	TOLERANCES	
FINISH: "BK" FINISH	x. x	± 0.20
MATERIAL: 2.0mm STEEL	x. xx	± 0.10
DATE: 01-4-5	ANGLES ± 0.50	
REV.		



PennElcom
hardware & fastener solutions

UNIT: MM	P/N: 3233-2	COMPONENT: HARDNESS: 52-57 (HRB)
NAME: SLIDE DRAWER		TOLERANCES
FINISH: "BK" FINISH		X. X ± 0.20
MATERIAL: 1.5mm STEEL		X. XX ± 0.10
DATE: 01-4-5		ANGLES ± 0.50
REV.		



PennElcom hardware & fastener solutions	
UNIT: MM	P/N: 3233-3
NAME: SLIDE DRAWER	COMPONENT: HARDNESS: 52-57 (HRB)
FINISH: "BK" FINISH	TOLERANCES
MATERIAL: 1.0mm STEEL	X. X ± 0.20
DATE: 01-4-5	X. XX ± 0.10
REV.	ANGLES ± 0.50