
Pomona®

Model 2259 Phenolic Box Component Mounting Double Plug To Binding Posts



MATERIALS:

Binding Posts: Insulated. Brass, Alloy 360, ½ Hard.

Finish: Nickel plated Insulation: Polycarbonate Colors: Black and Red

Banana Plug Springs: Beryllium Copper, Cond. H.T.

Finish: Nickel plated

Banana Plug Bodies and Solder Turret Terminals: Brass, Alloy 360 ½ Hard.

Finish: Nickel plated per QQ-N-290 Class 2 (.0002/.0003)

Molded Housing: Electrical grade Phenolic. Color: Black

Marking: "MODEL 2259 POMONA ELECTRONICS CALIF."

Cover: Phenolic Plate. Color: Black Screws: 2 ea. #2-56 x ¹/₄" Pan HD. - Steel

RATINGS:

Operating Temperature: +115°C. (+239°F.) Max.

Current: 15 Amperes

ORDERING INFORMATION: Model 2259

All dimensions are in inches. Tolerances (except noted): $.xx = \pm .02$ " (,51 mm), $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies. Made in USA

6/9/99 Sales: 800-490-2361 Fax: 888-403-3360
SY/EH/LS Technical Assistance: 800-241-2060