



### Main

Range	Thalassa
Product name	Thalassa TBS
Device application	Multi-purpose
Product or component type	Industrial box
Height	116 mm
Width	116 mm
Depth	133 mm
Internal height	105 mm
Internal width	105 mm
Internal depth	125 mm
Enclosure mounting	Wall mounted
Device composition	1 x body 1 x cover 4 x cover screw
Quantity per set	Set of 2
Body type	One piece moulded
Type of front cover	High plain cover
Cover fixing	Plastic screws
Lock type	Outside sealed area: flat screwdriver captive screw
Removable parts	Cover, by captive screws

### Complementary

Material	ABS
Colour	Grey ( RAL 7035 )
Standards	IEC 62208
Product certifications	SEMKO TÜV DEMKO

IP degree of protection	IP66conforming to NEMA 4.4X
IK degree of protection	IK07conforming to IEC 62262
Fire resistance	650 °C conforming to IEC 60695-2-11
Ambient air temperature for storage	-15...40 °C
Ambient air temperature for operation	-25...60 °C

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------