



### Overview

Model Name	APC Power-Saving Home/Office SurgeArrest, 8 Outlets with Phone Protection, 120V
Includes	Telephone Cable , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Aruba , Bahamas , Barbados , Belize , Bermuda , Canada , Colombia , Costa Rica , Cuba , Dominican Republic , Ecuador , El Salvador , Guatemala , Haiti , Honduras , Jamaica , Mexico , Nicaragua , Panama , Puerto Rico , Trinidad And Tobago , Turks And Caicos Islands , United States , Venezuela , VIRGIN ISLANDS (UNITED STATES)

### Output

Number of Outlets	8
Receptacle Style	NEMA 5-15R

### Input

Nominal Input Voltage	120V
Input Power	0 W
Input Frequency	50/60 Hz
Input Connections	NEMA 5-15P
Maximum Line Current per phase	0.0 A
Cord Length	1.83 meters
Maximum Input Current	15 A

### Surge Protection and Filtering

Surge energy rating	2160 joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	58.0 dB
Peak Current Common Mode	144.0 kA
NM Surge Response Time (ns)	1.0 ns
Data Line Protection	RJ-11 Modem/Fax protection (two wire single line)
Let Through Voltage Rating	400

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Physical

Net Weight	0.56 kg
Maximum Height	267.0 mm
Maximum Width	122.0 mm
Maximum Depth	38.0 mm
Shipping Weight	0.96 kg
Shipping Height	362.0 mm
Shipping Width	248.0 mm
Shipping Depth	44.0 mm
Master Carton Units	6.0
Master Carton Dimensions (Length x Width x Height)	14.6 x 12.87 x 16.3 inches
Master Carton Weight	7.18 kg
SCC Codes	1073130426922 6
Color	White
Units per Pallet	216.0

## Environmental

Operating Environment	0 - 45 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-5 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

## Conformance

Approvals	ETL , UL 1449
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$150000
UL 1449 TVSS Rating	<![CDATA[<400]]>

## Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs