

ATEX ZONE 0 INTRINSICALLY SAFE RIGHT ANGLE

ATEX-
RA2

Upgraded

LIGHT BY
CREE 
LEDs


REACH

IECE



RoHS

- » 270 Lumen white CREE LED
- » Zone 0 ATEX gas compliant
- » Suitable for mining
- » Safety release valve to release hydrogen gases
- » Chemical and corrosion resistant
- » Rubberised head and grips for durability
- » Ultra strength polycarbonate housing
- » Convenient pocket clip
- » Safety locking battery compartment
- » Easy push micro switch operation
- » IP54 dust and water resistant

7-13
HOURS
RUNTIME

250
METRE
BEAM RANGE

270
LUMENS
OUTPUT

IP54
DUST & WATER
RESISTANCE

BATTERY 4 x 1.5v AA Alkaline Batteries (not inc.)
WEIGHT 250g (without batteries)
DIMENSION 183 x 69 x 63mm



RIGHT ANGLE HEAD



ULTRA SMOOTH REFLECTOR



CONVENIENT REAR POCKET CLIP



ANTI-SLIP RUBBER GRIP HANDLE

