

Die Grinders
GG5 7



500W toolpost grinder with extension neck to facilitate clamping or used as extra hand support. Standard 8mm collet supplied. Suitable for grinding wheels up to 70mm diameter, rubber bonded polishing heads up to 50mm and vitrified points up to 45mm.

| | |
|---------------|----------|
| Model | GG5 7 |
| Input Power | 500 W |
| No Load Speed | 7000 rpm |
| Weight | 1.6 kg |

479281

| Voltage | Order Code | Price Each |
|---------|------------|------------|
| 230 | 135-8253 | |
| 110 | 135-8254 | |