Wire Termination Tools and Installation Kits

1½ tons of grip that weighs less than three pounds!

Battery-Powered Crimping Tool — BAT22-6

T&B's newest battery-powered tool is fast and portable for making highvolume and difficult-to-reach terminal installations in a snap. The Sta-Kon® BAT22-6 delivers 1.5 tons of crimping force with an easy, pushbutton trigger. The lightweight, ergonomic design minimizes the risk of repetitive motion injuries that can occur with traditional hand crimping tools. And at less than three pounds, one-hand operation is easy while still packing enough power to crimp up to #6 AWG terminals in seconds.

- Interchangeable dies can be guickly changed to crimp non-insulated and insulated terminals up to #6 AWG
- Dies are the same as our hand tools crimps will be exactly the same between Sta-Kon® hand tools such as our ERG4001 and the BAT22-6
- 360° rotating head gives the user the added flexibility when crimping hard-to-reach connections
- Short cycle time equates to crimping times of less than two seconds
- Quick, lightweight, and maneuverable
- NiCd battery operation provides long-lasting battery life to complete up to 150 crimps on a single charge
- Extra battery and charger are included with the tool, ensuring round-the-clock operation
- Battery charger provides full battery life in under
- Linear crimping motion gives a symmetric, high-quality crimp every time



Easy to rotate with your wrist - delivers fast and effective crimping power.



Uses the exact dies of the Comfort Crimp line of ergonomic tools for Sta-Kon® and Dragon Tooth® terminals.

Included Accessories


- Sturdy, plastic carrying case for portability
- Two 9.6V NiCd batteries and battery charger
- Sturdy tray for convenient storage of crimp dies

CAT. NO.	DESCRIPTION	PKG. QTY.	
BAT22-6	Battery Crimping Tool, 1.5 Ton with 120-VAC Charger	1	
Crimp Dies*			
DIE2001	Insulated #22–#10 AWG Sta-Kon® Terminals	1	
DIE2002	Non-Insulated #22-#10 AWG Sta-Kon® Terminals	1	
DIE2005	Non-Insulated #16-#14/#12-#10/#8-#6 Sta-Kon® Terminals (Tubular Only)	1	
DIE2007	Insulated #8–#6 AWG Sta-Kon® Terminals (Tubular Only)	1	
*Dies sold separately.			

Note: Battery-powered tools BPI42300CB, BPI T6BSCB and BPI T62BSCB can also be used to crimp non-insulated Sta-Kon® terminals. See pages F-86-F-88.

Portable heavy-duty air tool.

PAIR22-6 Heavy-Duty Portable Air Crimp Tool



- Crimps #22–#6 AWG terminals
- Installs Sta-Kon® terminals as well as ferrules and Dragon Tooth® connectors
- Interchangeable dies
- Open yoke enables easy access to insert and remove terminals for crimping





CAT. NO.	DESCRIPTION	PKG. QTY.	
PAIR22-6	Open yoke, hand actuated	1	
Crimp Dies*			
DIE2001	Insulated #22-#10 AWG Sta-Kon® Terminals	1	
DIE2002	Non-Insulated #22-#10 AWG Sta-Kon® Terminals	1	
DIE2005	Non-Insulated #16—#10/#8—#6 Sta-Kon® Terminals (Tubular Only)	1	
DIE2007	Insulated #8–#6 AWG Sta-Kon® Terminals (Tubular Only)	1	

* Dies sold separately.

Note: The dies for the BAIR22-6, PAIR22-6 and BAT22-6 are interchangeable.

Note: Battery-powered tools BPI42300CR, BPLT6BSCR and BPLT62BSCR can also be used

to crimp non-insulated Sta-Kon® terminals. See pages F-86-F-88.



Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354 Tel: 888.862.3289

