

## Universal Reversible USB 2.0 Hi-Speed Adapter (Reversible A to A M/F)

MODEL NUMBER: UR024-000



### Highlights

- Universal / Reversible A-Male plugs in any direction
- Turns a standard USB cable into a Universal Cable
- USB2.0 Rated

### Package Includes

- Universal Reversible USB 2.0 A-Male to A-Female Adapter

### Description

Tripp Lite's UR024-000, USB Male to Female adapter, features a Universal / Reversible Male end which allows the adapter to be plugged in any direction on a computer's USB port. Add this adapter to a standard USB cable, and convert it to a Universal pluggable cable. USB2.0 rated for 480mbps transfer rates. Fully molded, with gold plated contacts for a lifetime of use.

### Features

- USB 2.0 Male-to Female adapter, with Universal / Reversible Male connector
- Male end can be plugged in any direction
- USB2.0 Hi-Speed rated

## Specifications

INPUT	
Cable Length (ft.)	0
Cable Length (m)	0
PHYSICAL	
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	-10/+75° C (14 to 167° F)
Storage Temperature Range	-20/+80° C (-4 to 176° F)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<b>CONNECTIONS</b>	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	USB A (FEMALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>