



12-Outlet Vertical Power Strip, 120V, 15A, 6-ft. Cord, 5-15P, 36 in.

MODEL NUMBER: PS361206



Highlights

- Ideal for applications needing multiple convenience outlets for powering a variety of electronic equipment
- 36-in. mountable housing with 12 standard NEMA 5-15R outlets and a 6-ft. power cord
- Lighted, covered On/Off switch and 15-amp circuit breaker
- Sturdy construction and heavy-duty, all-metal housing

Package Includes

- PS361206
- Mounting hardware
- Instruction manual

Description

The PS361206 provides a 15-amp, 120v power strip with 12 standard NEMA 5-15R outlets in a rugged, all-metal, mountable housing. It allows for both vertical and horizontal mounting, making it ideal for a variety of uses including office, rackmount, workbench, industrial and telecom applications. With a NEMA 5-15P, 6-ft. power cord, you don't have to install the PS361206 next to outlets you already have; it can be mounted across the room and deliver reliable service where you need it most. A lighted and covered On/Off switch helps prevent accidental shut-offs, while a 15-amp circuit breaker guards against dangerous circuit overloads. Its sturdy all-metal extruded aluminum housing stands up to demanding network, laboratory or factory environments.

Features

Multi-Outlet Power Distribution: Featuring 12 outlets compatible with all standard electrical equipment, the PS361206 is an ideal solution for applications or locations that require power to many devices simultaneously. The 36-in. housing spaces the outlets 2.64 inches apart from center to center, allowing enough room for most AC adapters and transformers.

Vertical or Horizontal Mounting: With vertical or horizontal installation, a rugged housing and plenty of outlets, Tripp Lite's PS361206 is ideal for point-of-sale and retail display applications as it provides reliable, consistent power service for multiple devices. Tripp Lite's power outlet strips can also be used in home office, workbench and rack enclosure applications. The included mounting hardware allows the PS361206 to be installed wherever reliable, multi-outlet power distribution is required.

Premium Safety Features: The lighted On/Off switch features a translucent cover that eliminates accidental shut-offs while still allowing you to see whether the PS361206 is operational with a glance. A built-in, 15-amp circuit breaker prevents dangerous circuit overloads that could damage equipment. The breaker immediately shuts off AC input to the PS361206 when it detects that the equipment load is drawing too much power.

Heavy-Duty Housing: The PS361206's rugged, all-metal housing is durably constructed making it a great solution for industrial, retail display and workbench applications.

Specifications



OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(12) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Outlet Spacing	2.64 in.
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Connection Type	Nema 5-15P
Input Plug Features	Black
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Input Cord Gauge Type	14/3 SJT
Voltage Compatibility (VAC)	120
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Unit Dimensions (hwd / in.)	1.25 x 1.50 x 36.0
Unit Dimensions (hwd / cm)	3.18 x 3.81 x 91.4
Unit Weight (lbs.)	2.27
Unit Weight (kg)	1.03
Material of Construction	Aluminum
Included Mounting Accessories	Includes mounting clips
Receptacle Color	Gray
Color (AC Line Cord)	Gray
Form Factors Supported	Supports vertical or horizontal mounting in rack enclosures, raceways and a variety of other applications
Outlets Measurement (Center to Center)	2.65 in
CERTIFICATIONS	
UL1363 (Power Tap)	UL1363



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

cUL / CSA (Canada)	cUL
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>