

EK EKPE 130 G



Sample photo

Order symbol: EKPE 130 G
Product nbr: 2538043
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074013583
EI. number:
 Finland: 3425421
 Electric No. Italy: 7501045
 Electric No. Sweden: 2538043

Including: Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	380	280	130	EKPG	Base, PC
inch:	15.0	11.0	5.1	EKP 30-G	Cover
				EKP 80-G	Cover

Materials:

Material: Polycarbonate
Base colour: RAL 7035 -light grey
Cover screws material: Polyamide
Cover colour: RAL 7035 -light grey
Cover screws colour: Grey
Gasket material: Polyurethane

Accessories:

EKP 30-T Cover
 EKP 80-T Cover
 EKPVT Mounting plate
 EKPXT Mounting plate isolated
 EKV 22 DIN-35 Mounting rail
 EKV 32 DIN-35 Mounting rail
 EKPZR Extension frame

Temperatures:

Temperature °C (short term): -40 ... 120 °C
Temperature °C (continuous): -40 ... 80 °C
Temperature °F (short term): -40 ... 250 °F
Temperature °F (continuous): -40 ... 175 °F

Rating:

Ingress Protection (EN 60529): IP66/IP67
 Impact Resistance (EN 62262): IK08
 Electrical insulation: Totally insulated
 Halogen free (DIN/VDE 0472, Part 815): 1
 UV resistance: UL 508
 Flammability Rating: UL 746C 5"
 Glow Wire Test (IEC 695-2-1) °C: 960
 NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

Accessories:

EKPE Base, PC

Certificates:

Germanischer Lloyd (GL)
 SGS Fimko
 Lloyds Register of Shipping (LR)
 Gost R

