

PICCOLO PC C 65 T



Sample photo

Order symbol: PC C 65 T
Product nbr: 8724005
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074002020
El. number:
 Finland: 3423505
 Electric No. 8212001527
 Denmark:
 Electric No. Italy: 7202020
 Electric No. Sweden: 2536838

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	140	80	65	CHM-3	DIN-35 Mounting rail
inch:	5.5	3.1	2.6	FP 22040	Wall fastening lug (2 pcs)

Materials:		Rating:	
Material:	Polycarbonate	Ingress Protection (EN 60529): IP66/IP67	
Base colour:	RAL 7035 -light grey	Impact Resistance (EN 62262): IK08	
Cover screws material:	Polyamide	Electrical insulation: Totally insulated	
Cover colour:	Clear transparent	Halogen free (DIN/VDE 0472, Part 815): 1	
Cover screws colour:	Grey	UV resistance: UL 508	
Gasket material:	Polyurethane	Flammability Rating: UL 746C 5"	
		Glow Wire Test (IEC 695-2-1) °C: 960	
		NEMA Class: NEMA 1, 4X, 6, 12, 13	

Temperatures:		Certificates:	
Temperature °C (short term):	-40 ... 120 °C	Germanischer Lloyd (GL)	
Temperature °C (continuous):	-40 ... 80 °C	SGS Fimko	
Temperature °F (short term):	-40 ... 250 °F	Gost R	
Temperature °F (continuous):	-40 ... 175 °F		

Accessories:	
C-MP	Mounting plate

