



Sample photo

**Order symbol:** CAB ABS 403018 G3B  
**Product nbr:** 8183352  
**Description:** Cabinet, ABS, Grey door  
**Remarks:** Locks on the long side

**EAN:** 6418074020307  
**El. number:**  
Finland: 3424318  
Electric No. Denmark: 8212019043  
Electric No. Italy: 7811045  
Electric No. Sweden: 2540075

Including: Cabinet base, door with PUR gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

| Dimensions: | Length | Width | Height |
|-------------|--------|-------|--------|
| mm:         | 400    | 300   | 180    |
| inch:       | 15.7   | 11.8  | 7.1    |

#### Materials:

**Material:** ABS  
**Base colour:** RAL 7035 -light grey  
**Cover colour:** RAL 7035 -light grey  
**Gasket material:** Polyurethane

#### Temperatures:

**Temperature °C (short term):** -40 ... 80 °C  
**Temperature °C (continuous):** -40 ... 60 °C  
**Temperature °F (short term):** -40 ... 175 °F  
**Temperature °F (continuous):** -40 ... 140 °F

#### Accessories:

EKIV 43 Mounting plate

#### Accessories:

EKIV 43 PL Mounting plate, Plastic  
EKIV 27 DIN-35 Mounting rail  
DS35270E1 DIN-35 Mounting rail  
EKIV 37 DIN-35 Mounting rail  
DS35370E1 DIN-35 Mounting rail  
FP A 43 Swing-out door/Front plate  
MB 12225 AL Swing door set  
FP 43 Front plate  
FP 12x2-43 Front plate  
FP 12x3-43 Front plate  
DRF 43/44 DIN rail frame set

#### Rating:

Ingress Protection (EN 60529): IP65  
Impact Resistance (EN 62262): IK08  
Electrical insulation: Totally insulated  
Halogen free (DIN/VDE 0472, Part 815): 1  
Flammability Rating: UL 94 HB  
Glow Wire Test (IEC 695-2-1) °C: 650  
NEMA Class: NEMA 1, 4, 4X, 12, 13

#### Certificates:

SGS Fimko  
Gost R

