

CARDMASTER ABS 25/22-3



Order symbol: ABS 25/22-3
Product nbr: 7585134
Description: Enclosure, ABS
Remarks: Smoked transparent hinged cover

EAN: 6418074059406
EI. number:
Finland: 3438244
Electric No. Sweden: 7585134

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:		Length	Width	Height	Accessories:	
mm:		280	219	156	FP 25/22	Front plate (aluminium)
inch:		11.0	8.6	6.1	FC PC 25/22	Frame of PC front plate
Materials:				Rating:		
Material:	ABS			Ingress Protection (EN 60529): IP65		
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK07		
Cover colour:	Smoked grey			Electrical insulation: Totally insulated		
Gasket material:	EPDM & PUR			Halogen free (DIN/VDE 0472, Part 815): 1		
Temperatures:				Flammability Rating: UL 94 HB		
Temperature °C (short term):	-40 ... 80 °C			Glow Wire Test (IEC 695-2-1) °C: 650		
Temperature °C (continuous):	-40 ... 60 °C			NEMA Class: NEMA 1, 3, 3R, 12, 13		
Temperature °F (short term):	-40 ... 175 °F			Certificates:		
Temperature °F (continuous):	-40 ... 140 °F			Gost R		
Accessories:						
MP 25/22	Mounting plate					

