



Order symbol: TA342912
Product nbr: 5814004
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074060761
EI. number:
Finland: 3435690
Electric No. Denmark: 8212035085
Electric No. Sweden: 5814004

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Sample photo

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	344	289	117	ARH 2328	DIN-35 Mounting rail
inch:	13.5	11.4	4.6	DR 316	DIN-35 Mounting rail
Materials:				FP 10674	
Material:	ABS			DPS 14553	Grey sealing plug set
Base colour:	RAL 7035 -light grey			Rating:	
Cover screws material:	Polyamide			Ingress Protection (EN 60529): IP65	
Cover colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK07	
Cover screws colour:	Grey			Electrical insulation: Totally insulated	
Gasket material:	Polyurethane			Halogen free (DIN/VDE 0472, Part 815): 1	
Temperatures:				Flammability Rating: UL 94 HB	
Temperature °C (short term):	-40 ... 80 °C			Glow Wire Test (IEC 695-2-1) °C: 650	
Temperature °C (continuous):	-40 ... 60 °C			Certificates:	
Temperature °F (short term):	-40 ... 175 °F			SGS Fimko	
Temperature °F (continuous):	-40 ... 140 °F				
Accessories:					
MP 3429	Mounting plate				

