

**SOLID PC 5628 13 T-3FSH**



Sample photo

**Order symbol:** PC 5628 13 T-3FSH  
**Product nbr:** 2539555  
**Description:** Enclosure, PC  
**Remarks:** Transparent hinged cover

**EAN:** 6418074052872  
**EI. number:**  
 Finland: 3435756  
 Electric No. Sweden: 2539555

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:			Accessories:		
Length	Width	Height			
mm:	558	278	130	EKTX	Mounting plate isolated
inch:	22.0	10.9	5.1	EKV 22	DIN-35 Mounting rail
<b>Materials:</b>			EKV 50	DIN-35 Mounting rail	
<b>Material:</b>	Polycarbonate		EKTZR	Extension frame	
<b>Base colour:</b>	RAL 7035 -light grey		<b>Rating:</b>		
<b>Cover screws material:</b>	Polyamide		Ingress Protection (EN 60529): IP65		
<b>Cover colour:</b>	Clear transparent		Impact Resistance (EN 62262): IK08/IK09		
<b>Cover screws colour:</b>	Grey		Electrical insulation: Totally insulated		
<b>Gasket material:</b>	Polyurethane		Halogen free (DIN/VDE 0472, Part 815): 1		
<b>Temperatures:</b>			UV resistance: UL 508		
<b>Temperature °C (short term):</b>	-40 ... 120 °C		Flammability Rating: UL 746C 5"		
<b>Temperature °C (continuous):</b>	-40 ... 80 °C		Glow Wire Test (IEC 695-2-1) °C: 960		
<b>Temperature °F (short term):</b>	-40 ... 250 °F		<b>Certificates:</b>		
<b>Temperature °F (continuous):</b>	-40 ... 175 °F		SGS Fimko		
<b>Accessories:</b>			Gost R		
EKTVT	Mounting plate				

