



Sample photo

Order symbol: ABS F 85 G
Product nbr: 8784312
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074002259
El. number:
Finland: 3423465
Electric No. Denmark: 8212001954
Electric No. Italy: 7211045
Electric No. Sweden: 2536723

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:				Accessories:	
mm:	230	80	85	FM-3	DIN-35 Mounting rail
inch:	9.1	3.1	3.3	FP 22040	Wall fastening lug (2 pcs)
Materials:				Rating:	
Material:	ABS			Ingress Protection (EN 60529): IP66/IP67	
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK07	
Cover screws material:	Polyamide			Electrical insulation: Totally insulated	
Cover colour:	RAL 7035 -light grey			Halogen free (DIN/VDE 0472, Part 815): 1	
Cover screws colour:	Grey			Flammability Rating: UL 94 HB	
Gasket material:	Polyurethane			Glow Wire Test (IEC 695-2-1) °C: 650	
				NEMA Class: NEMA 1, 4X, 6, 12, 13	
Temperatures:					
Temperature °C (short term):	-40 ... 80 °C				
Temperature °C (continuous):	-40 ... 60 °C				
Temperature °F (short term):	-40 ... 175 °F				
Temperature °F (continuous):	-40 ... 140 °F				
Accessories:					
F-MP	Mounting plate				

PICCOLO 230x80x65-85

