



## IEC Type K, J or T PFA Exposed Welded Tip Thermocouples with Miniature Thermocouple Plug



### About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors.

### Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

### Contact Details

Email  
sales@labfacility.com

Website  
www.labfacility.com

- ◆ Thermocouple types K, J or T to IEC 584
- ◆ Fast response, welded exposed junction
- ◆ Teflon® PFA insulated twin-twisted lead
- ◆ Class 1 cable specification in accordance with BS EN 60584-3:2008
- ◆ Tolerance to IEC 584 Class 1
- ◆ Miniature plug termination
- ◆ Temperature range -75°C to +250°C
- ◆ Ideal for test & development applications

Thermocouple type	Conductors	Length	order code
Type K	1/0.315mm	2 metre	XF-1225-FAR
Type K	7/0.2mm	2 metre	XF-1226-FAR
Type K	1/0.2mm	2 metre	XF-1227-FAR
Type K	1/0.2mm	10 metre	XF-1228-FAR
Type J	1/0.2mm	2 metre	XF-1229-FAR
Type T	1/0.315mm	1 metre	XF-1230-FAR
Type T	1/0.315mm	2 metre	XF-1231-FAR
Type T	7/0.2mm	1 metre	XF-1232-FAR
Type T	7/0.2mm	2 metre	XF-1233-FAR
Type T	1/0.2mm	2 metre	XF-1234-FAR