

## Torque screwdriver iTorque® with digital scale (36888) 1,0-5,0 Nm, 9-44 in.lbs, 4 mm



**Article No.:** 36888

**GTIN:** 4010995368883

**Price Gross:** 190,86 EUR

**Unit:** Piece

**Meets your requirements:** A variably settable torque which covers a large range of usage.

**Lowers your costs:** The correct torque protects you from warranty claims.

**Increases your efficiency:** The correct torque avoids damaging material and no follow-up work is necessary.

**Increases your productivity:** Utmost process safety thanks to integrated ClickControl counting function and calibration alarm.

**Standards:** DIN EN ISO 6789.

---

|                       |   |
|-----------------------|---|
| Tolerance             | 6%  |
| Hex                   | 4 mm  |
| Handle_length         | 134 mm  |
| Handle_diameter       | 40 mm   |
| Nm                    | 1,0-5,0 Nm  |
| Weight                | 373 g   |
| lbs                   | 9-44 in.lbs   |
| Serie                 | 2.835   |
| Anwendungsszenarien   | For applications where recommended torque settings are important.<br>Use in combination with a Wiha torque interchangeable blade. |
| Customs tariff number | 82054000  |
| Product group         | 36888   |