

# My Book™ Premium Edition™

USB 2.0/Firewire® 400  
Backup Software  
Capacity Gauge



## INTERFACE

USB 2.0  
FireWire® 400

## SOFTWARE

WD Backup™  
Google™

## CAPACITIES

160 to 500 GB

## ORDER NUMBERS

WDG1C1600x  
WDG1C2500x  
WDG1C3200x  
WDG1C4000x  
WDG1C5000x

**Note:** Not all products may be available in all regions of the world.

They're your photos, your music, your videos, your important files. Make extra room for them, back them up, and keep them safe on YOUR Book. WD's My Book Premium is the perfect external hard drive for all your precious digital assets.

## Product Features

- **WD Backup** — Exceptionally easy-to-use software lets you back up just your photos, video, and music. Back up specific folders, or back up all your files with a few simple steps. Set a scheduled backup and forget it — your files will be backup up automatically.
- **Google software** — Search your drive, manage your photos, and simplify Web searches with included Google software.
- **Dual interface** — For all-out, high-speed performance, FireWire 400 is the interface of choice. For convenience and compatibility among multiple computers, USB 2.0 is the way to go. How do you choose? With this drive, you don't have to choose — you get both interfaces on the same drive.
- **Capacity gauge** — See at a glance how much space is available on your drive.
- **Intelligent drive management** — SmartPower™ automatic power on/off, Safe Shutdown™, and LED activity lights make this drive especially easy to use.
- **Smart design** — The elegant case, iconic of a book, takes up less space on your desk, stacks horizontally, and allows two or more drives to nestle neatly together like volumes on a shelf.
- **High quality hard drive** — Inside the case is an exceptionally fast (7200 RPM spin speed), ultra quiet, cool-running hard drive from WD, of course!
- **One-year warranty in the U.S., two-year warranty in Europe**

## Compatibility

### Windows®

- Available USB or FireWire port
- Windows 98SE/Me/2000/XP

### Macintosh®

- Available USB or FireWire port
- Mac® OS X 10.2.8 or later

## The WD Promise



WD understands the importance of the information you save to your hard drive and we are committed to protecting that data with exceptionally reliable products, advanced data protection technology, and superior customer support. No one does more to safeguard your data than WD.

# My Book Premium Edition



## Performance Specifications

Buffer	8 MB
160, 250, 320 GB	16 MB
400, 500 GB	
Data transfer rate	
USB	480 Mb/s (maximum)
FireWire	400 Mb/s (maximum)
Read seek time	8.9 ms (average)
Rotational speed	7200 RPM

## Environmental Specifications

Operating temperature	5°C to 35°C
Non-operating temperature	-20°C to 65°C

## Power Specifications

AC input voltage	100-240V
AC input frequency	47-63 Hz

Google™



RoHS



## Product Dimensions

Height	6.78 in (172.2 mm)
Length	5.63 in (143.0 mm)
Width	2.23 in (56.7 mm)
Weight	2.6 lb (1.2 kg)

## Packaging Specifications

Box	English	Metric
Retail package size	11.625 in × 4.5 in × 8.0 in	295.275 mm × 114.3 mm × 203.2 mm
Retail package weight	4.55 lb	2.06 kg
Master carton size	11.94 in × 9.31 in × 8.63 in	303.28 mm × 236.47 mm × 219.2 mm
Master carton weight	9.75 lb	4.42 kg
Packages per master carton	2	2
Master cartons per pallet	80	80

## Retail UPC Codes

AMERICAS			EUROPE/MIDDLE EAST/AFRICA	
Capacity <sup>1</sup>	Order Number	UPC Code	Order Number	UPC Code
160 GB	WDG1C1600N	7 18037 11651 8	WDG1C1600E	7 18037 11655 6
250 GB	WDG1C2500N	7 18037 11653 2	WDG1C2500E	7 18037 11657 0
320 GB	WDG1C3200N	7 18037 11654 9	WDG1C3200E	7 18037 11658 7
400 GB	WDG1C4000N	7 18037 11711 9	WDG1C4000E	7 18037 11712 6
500 GB	WDG1C5000N	7 18037 11713 3	WDG1C5000E	7 18037 11714 0

## For service and literature:

[support.wdc.com](http://support.wdc.com)  
[www.westerndigital.com](http://www.westerndigital.com)

800.ASK.4WDC North America  
949.672.7199 Spanish  
+800.6008.6008 Asia Pacific  
+31.20.4467651 EMEA

Western Digital and WD are registered trademarks; and the WD logo, WD Backup, FIT Lab, My Book, Safe Shutdown, and SmartPower are trademarks of Western Digital Technologies, Inc. Other marks may be mentioned herein that belong to other companies. Product specifications subject to change without notice.

© 2006 Western Digital Technologies, Inc. All rights reserved.

Western Digital  
20511 Lake Forest Drive  
Lake Forest, California 92630  
U.S.A.

2879-001167-A04 Jun 2006

<sup>1</sup> 1 gigabyte (GB) = 1 billion bytes. Total accessible capacity varies depending on operating environment.

