

# 2-Port USB KVM Switch with Cables and Remote

GCS22U



- One USB keyboard, USB mouse, and VGA monitor control two computers
- Max resolution: 2048 x 1536, DDC2B
- Plug-n-Play monitor support
- 3' long molded-in cables to simplify setup
- Compact design features two attached KVM (USB and VGA) cables
- Compatible with PC, MAC and SUN operating platforms
- Supports Windows 2000 or higher, Mac OS 9.0 or higher, Sun Solaris 9 or higher
- No software drivers required – simply connect the cables to the computers
- Computer selection via 6 ft remote control cable that can be placed on your desk for easy reach
- Full Mac keyboard support
- Supports programmable mice
- No power adapter required
- 3 Year Limited Warranty

The IOGEAR 2-Port USB Cable KVM allows users to share a VGA monitor, a USB mouse, and a USB keyboard between two computers. Users can switch between computers using the wired remote switch button that can be placed on your desk for convenience. It offers an out-of-box solution with no additional cables needed. It supports multiple operating systems including Windows, Sun, and Mac. It is entirely plug-n-play and requires no software to run. It is also powered through the USB bus and thus does not require a power supply to run. It is the ideal KVM for those who want a competitively priced, entry level KVM that will allow them to multitask with two computers at their disposal.

## 2-Port USB KVM Switch with Cables and Remote

### How does it work?

- Connect your monitor, keyboard and mouse to the KVM
- Connect the KVM USB cables to each computer
- Press the button on the remote controller to switch computers



### Requirements:

- Console
  - 1 VGA display
  - 1 set of USB keyboard and mouse

### Computers

- 1 VGA port
- 2 USB ports

### Operating Systems

- Windows XP, Windows Vista (32-bit / 64-bit)
- Mac OS X v10.3.9 or later
- Sun Solaris
- Linux

### Package Contents:

- 1 x 2-Port USB Cable KVM
- 1 x Quick Start Guide
- 1 x Warranty Card

### SPECIFICATIONS

Function	
CPU Connectors	
Monitor	VGA
Keyboard & Mouse	USB
Console Connectors	
Monitor	VGA
Keyboard & Mouse	USB
Cable Length	2 x 3 ft ea
Cable Type	Bonded USB
Connectors	
Keyboard	USB
Mouse	USB
Video Input	VGA

Dimensions	
POP Information	
10" Peg Hook	3
Unit Dimensions	
Width	3 in
Height	.87 in
Depth	2.5 in
Inner Pack	
Width	12.5 in
Height	8.25 in
Depth	
Inner Pack Qty.	6
Unit Package Dimensions	
Width	7.4 in
Height	7.6 in
Depth	2.25 in
Master Carton	
Width	13.25 in
Height	9.4 in
Depth	16.25 in
Master Carton Qty.	12
Weight	
Master Carton Wt.	13.6 lbs
Inner Pack Wt.	6.2 lbs
Unit Pack Wt.	1.0 lb
Unit Wt.	14 oz