TP-LINK®

Archer C7 AC1750 Wireless Dual Band Gigabit Router

• Features:

- The next generation of Wi-Fi, leading 802.11ac standard
- Simultaneous 5GHz 1300Mbps and 2.4GHz 450Mbps connections for 1.75 Gbps of total available bandwidth
- Full gigabit ports ensure ultra fast data transfer speeds
- 3*5dBi external antennas and 3 internal antennas provide maximum whole directional wireless coverage and reliability
- Dual USB Ports easily share printers, files or media with your friends or family locally or over the internet
- The device's built-in print server supports wireless printing from different computers by connecting a USB printer to the router
- Guest Network Access provides secure Wi-Fi access for guests sharing your home or office network
- Supports IPV6 (Internet Protocol Version 6)
- Wireless On/Off Switch lets you simply turn the wireless radio on
- Easy one-touch wireless security encryption with the WPS button
- Parental Control allows administrators to establish restricted access for children or staff





Dual Band



1300Mbps

+450Mbps



Range





USB Ports







Connection Enabled

• Description:

The TP-LINK's Archer C7 upgrades your network to the next generation of Wi-Fi. With combined wireless speeds of up to 1.75Gbps and 6 antennas, the device provides ultimate speeds and wireless range. You can run multiple bandwidth intensive applications in a large home or office. Simple tasks like sending e-mails or web browsing can be handled by the 2.4GHz band while bandwidth intensive tasks like online gaming or HD video streaming can be processed by the 5GHz band- all at the same time.

If you prefer a wired connection, the Archer C7 boasts five gigabit ports to provide a lightning-fast and lag-free experience. The two USB 2.0 ports will allow you to power a robust home Internet network by sharing printers, flash storage, ftp servers, or media players.

Archer C7 AC1750 Wireless Dual Band Gigabit Router


• Specifications:

HARDWARE FEATURES	
Interface	4 10/100/1000Mbps LAN Ports 1 10/100/1000Mbps WAN Port 2 USB 2.0 Port
Button	WPS/Reset Button Wireless On/Off Switch Power On/Off Button
External Power Supply	12VDC / 2.5A
Antenna type	Three 5GHz 5dBi detachable antennas (RP-SMA)
	Three 2.4GHz internal antennas
WIRELESS FEATURES	
Wireless Standards	IEEE 802.11a/n/ac, 5GHz
-	IEEE 802.11b/g/n, 2,4GHz
Frequency	2.4GHz and 5GHz
Signal Rate	5GHz: Up to 1300Mbps
EIRP	2.4GHz: Up to 450Mbps <20dBm
EIRP	5GHz
	11a 6Mbps: -96dBm, 11a 54Mbps: -79dBm
	11ac HT20: -71dBm, 11ac HT40: -66dBm, 11ac HT80: -63dBm
Reception Sensitivity	
,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	2.4GHz
	11g 54M: -77dBm
Mindon Francisco	11n HT20: -74dBm, 11n HT40: -72dBm
Wireless Functions	Enable/Disable Wireless Radio, WDS Bridge, WMM, Wireless Statistics
Wireless Security	WEP, WPA / WPA2, WPA-PSK/ WPA2-PSK encryption
SOFTWARE FEATURES	Dynamic IP/Static IP/PPPoE/PPTP(Dual Access)/L2TP(Dual Access)/BigPond
WAN Type	
DHCP	Server, Client, DHCP Client List, Address Reservation
Quality of Service	WMM, Bandwidth Control
Port Forwarding	Virtual Server, Port Triggering, UPnP, DMZ
Dynamic DNS	DynDns, Comexe, NO-IP
VPN Pass-Through	PPTP, L2TP, IPSec
Access Control	Parental Control, Local Management Control, Host List, Access Schedule, Rule Management
Firewall Security	DoS, SPI Firewall IP Address Filter/MAC Address Filter/Domain Filter IP and MAC Address Binding
USB Sharing	Support Samba(Storage)/FTP Server/Media Server/Printer Server
Management	Access Control
Management	Local Management Remote Management
	hemote management

Specifications:

OTHERS	
Certifications	CE, FCC, RoHS
System Requirements	Microsoft Windows 8/7/Vista/XP/2000/NT/98SE, MAC OS, NetWare,
, ,	UNIX or Linux.
Dimensions (W X D X H)	9.6 x 6.4 x 1.3 in. (243 x 160.6 x 32.5mm)
	Operating Temperature: 0° C \sim 40 $^{\circ}$ C (32 $^{\circ}$ F \sim 104 $^{\circ}$ F)
Environment	Storage Temperature: -40 $^{\circ}$ C ~70 $^{\circ}$ C (-40 $^{\circ}$ F ~158 $^{\circ}$ F)
2	Operating Humidity: 10%~90% non-condensing
	Storage Humidity: 5%~90% non-condensing

• Diagram:



Package:

- Archer C7 AC1750 Wireless Dual Band Gigabit Router
- 3 detachable antennas
- Power supply unit
- Resource CD
- Ethernet Cable
- Ouick Installation Guide

Related Products:

- Archer T4U AC1200 Wireless
 Dual Band USB Adapter
- Archer T2U AC600 Wireless Dual Band USB Adapter

¹Some USB hard drive that works at a high power without using any external power adapter might not be supported.

²The USB Printer Controller supports Windows 8/7/Vista/XP 32/64bits and Mac OS. For the printer compatibility information, please visit www.tp-link.com