

IP68/IP69K Plug & Socket Micro-Connector

Product Features

- Miniaturised The smallest connector on the market with a diameter of only 14mm
- Unique dimensions which can be used with wires up to 1.5mm²
- Quick Push-Pull Connection And Disconnection
- Ideal for Architectural Lighting, Lighting In Water, Led Connections, Street Lighting, Indoor Lighting, Urban Lighting, Advertising Billboards And Road Signs
- Tested and approved to resist dust and water (IP68 30 m / 1 h) and high pressure water (IP69K)





Product Codes

Image	Code	Туре	Cable min - max
Connector cable to cable			
	THB.381.A2A.L	Plug	7.0 mm - 8.0 mm
	THB.381.A2B.L	Plug (disconnection with a tool acc. EN 61535)	7.0 mm - 8.0 mm
	THB.381.A2A	Plug	5.8 mm - 6.9 mm
	THB.381.A2B	Plug (disconnection with a tool acc. EN 61535)	5.8 mm - 6.9 mm
	THB.381.B2A.L	Socket	7.0 mm - 8.0 mm
OF THE PARTY OF TH	THB.381.B2A	Socket	5.8 mm - 6.9 mm

Accessories			
0	6000448GT	Closure cap IP68 for socket	-
0	6000447GT	Closure cap IP68 for plug	-
•	6000473GT	Cable reduction	3.0 mm - 5.5 mm
	6000461GT	Cable reduction for 2-single pole cables	1.9 mm - 2.5 mm
~	6000462KC	special spanner for quick installation	-





Image	Code	Туре	Cable min - max
Connector panel-mounted			
	THB.381.N2A	Plug M16	-
	THB.381.N2B	Plug M16 (disconnection with a tool acc. EN 61535)	-
=0	THB.381.L2A	Plug M11	-
	THB.381.L2B	Plug M11 (disconnection with a tool acc. EN 61535)	-
	THB.381.P2A	Socket M16	-
e Elle	THB.381.M2A	Socket M11	-



URBAN LIGHTING STREET LIGHTING **ARCHITECTURAL LIGHTING**