

Rechargeable floodlight in a new design!

Mobile battery SMD LED lights

Technical highlights

- For indoor and outdoor use, IP 54
- Bright working light at any time, also at locations without power connection.
- Exchangeable lithium-ion battery.
- With integrated overcharging / total discharge protection and battery condition display.
- With On/off switch, with 1171260211 in addition with 2 different brightness levels (50%/100%).
- Only for 1171260211: USB charging connection 1.0 A for devices with USB charging cable such as smart phones, MP3 players, navigation units, etc.
- Including mains adapter and vehicle charging cable.
- Housing made of die-cast aluminium and high-quality plastic.
- Stable steel tube frame with slip-resistant rubber feet.



1171260111



1171260211

Technical data

Type designation	ML DA 1206 DE 3993	ML DA 2407 DE 3993
Art. no.	1171260111	1171260211
EAN	4007123641567	4007123641574
Power consumption	10W	20W
Luminous flux	730lm	1550lm
Colour temperature	5900K	5900K
IP class	IP54	IP54
Life cycle LED	50,000h	50,000h
Radiation angle	ca. 105°	ca. 105°
Protection class	III	III
Lithium-ion battery	11.1V / 2200mAh	11.1V / 4400mAh
Charging duration	ca. 3-4h	ca. 3h
Lighting duration	ca. 3h	3h (100%), 6h (50%)
USB output	not included	5V, max. 1000mA
Mains adapter input power	100-240V AC, 50/60Hz, max. 0.2A	100-240V AC, 50/60Hz, max. 0.2A
Mains adapter output power	15V DC, 0.75A	15V DC, 1.5A
Vehicle charging cable	12V DC / max. 3A	12-24V DC / max. 3A
Operating temperature	-10°C - +40°C	-10°C - +40°C
Dimensions	23.7x15.7x14.6cm	28.9x21.1x20.5cm

Scope of delivery / art. No. / EAN no.

- Including mains adapter and vehicle charging cable
- Packed in a coloured sales cardboard box

- PU: 1
- Available from August 2017
- Replacement battery: 1171260080 (for 1171260111) and 1171260070 (for 1171260211)



only for
1171260211