

Our classic light now also with LEDs!

Oval LED light L DN 3002 IP44 / L DN 5402 IP44

Technical Highlights

- Ideal for garage, basement, workshop or outside.
- Compact LED oval lamp made of plastic with a translucent cover.
- Can be mounted on the ceiling or wall.
- Uses approx. 80% less energy than conventional light sources.
- Instant bright light.
- Extremely long LED service life, impact-proof, maintenance-free.
- Color: light gray
- With GS certificate



Specifications

Type	L DN 3002 IP44	L DN 5402 IP44
Item No.	1270780	1270790
EAN	4007123641680	4007123641697
Supply voltage	220-240V 50Hz	220-240V 50Hz
Output	5.5W	10W
Light current	460 lm	800 lm
Efficiency	84 lm/W	80 lm/W
Weighted energy consumption	5.5 kWh/1000h	10 kWh/1000h
Energy efficiency category	A+	A+
Color temperature	6400K	6400K
Protection class	IP44	IP44
LED service life	50,000 hrs	50,000 hrs
Beam angle	> 120°	> 120°
Protection class	II	II
Operating temperature	-15°C – +40 °C	-15°C – +40 °C
Dimensions	12.7 x 7.0 x 17.5 cm	12.7 x 7.0 x 17.5 cm
Weight	0.2kg	0.25kg



Content/ Item No./ EAN

- Colorful display carton
- Item No. / EAN see above
- PU: 1
- Available February 2017

brennenstuhl®

Diese Leuchte enthält eingebaute LED-Lampen.

} L
E
D

Die Lampen können in der Leuchte nicht ausgetauscht werden.

874/2012