

Accessories
ZQB 2.5-2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com

**167712 ZQB 2.5****Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

General ordering data

Type	ZQB 2.5-2
Order No.	1677120000
Version	Accessories, Cross-connector bridge, 24 A
GTIN (EAN)	4008190467678
Qty.	50 pc(s).

Accessories
ZQB 2.5-2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	1.8 mm	Width (inches)	0.071 inch
Height	8.5 mm	Height (inches)	0.335 inch
Depth	21.85 mm	Depth (inches)	0.86 inch
Net weight	0.74 g		

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C
----------------------------------	--------	----------------------------------	--------

Material data

Material	Wemid	Colour	Yellow
UL 94 flammability rating	V-0		

System specifications

Version	For the terminals	Mounting rail	none
---------	-------------------	---------------	------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Plugged		

Dimensions

Pitch in mm (P)	5 mm
-----------------	------

Rating data

Rated current	24 A
---------------	------

Classifications

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC000489
UNSPSC	30-21-18-01	eClass 5.1	27-14-11-40
eClass 6.2	27-14-11-40	eClass 7.1	27-14-11-40
eClass 8.1	27-14-11-40	eClass 9.0	27-14-11-40
eClass 9.1	27-14-11-40		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S