

MA120

Professional mixing amplifier 120W



The revolutionary Apart MA120 mixing amplifier offers the end-user an unseen cutting-edge design and ease-of-use. The ground-breaking intuitive front panel is clear and easy to use without any unnecessary bells and whistles. The volume control rotary on the front panel is prominent, illuminated, bigger and put in the forefront while the mic volume control is smaller and recessed. The unit offers 120 watts in 70 or 100 volt mode and comes with two mic/line inputs and four stereo line, mono summed inputs.

The refreshing rear panel will give every installer an instant gratification due to the sheer and logic design. Together with an unprecedented connectivity and immaculate sound performance these reliable mixing amplifiers will conquer the fixed-install audio market.

TECHNICAL SPECIFICATIONS

19" (483 mm wide) rack mounting	yes	height- rack units (1U=44 mm) in U	2
depth (build in) in mm	290	depth (incl front) in mm	300
power supply	100 - 240 VAC	power consumption (max) in watts	160
output power RMS 100 volts in watts	120	output power RMS 4 ohms in watts	120
dynamic output power 100 volts in watts	120	minimum impedance load in ohms	4
output power tapings	70 - 100 volts - 4 ohms	zone outputs	1
MIC inputs balanced	3	inputs with Phantom power	2
line input unbalanced	4	tone control	yes
priority switch	2	VOX mute	yes
chime	yes	emergency input	1
priority output	1	priority levels	4
power amp topology	class-D	frequency response (in Hz)	60 - 20 k
cooling system	convection	applicable in 100V	yes
applicable low impedance	yes	Net weight product (kg)	5

MORE PICTURES

