



Proinstall-100-CH



Product Overview

Combined installation meter

Functions

- Loop resistance measurement
- Line internal resistance measurement
- Short circuit current measurement
- Low impedance and continuity measurement
- Insulation measurement
- RCD / FI measurement (contact voltage, tripping time, tripping current - rising current)

- Voltage and frequency measurement

Device information

- Memory for approx. 400 measurements with 3 levels for allocation of distributor and circuit numbers
- IR / USB interface for transfer of the stored measured values to the PC
- Software for logging optionally available for the printout of a test report
- Integrated socket test with touch electrode to determine incorrectly connected Sockets or missing protective conductor
- Easy-to-read, large LC display with background lighting and a particularly large viewing angle
- Auto power off

Product highlights

- Compact and rugged design allows you to work even under difficult conditions (weighs only 1500g)
- Easy to use, intuitive user interface allows you immediately and to work efficiently
- Test probe with test button supplied available
- loop resistance measurement and short circuit current measurement without tripping the RCD / FI