



Datenblatt - Fiche technique - Data sheet

11.02.8753



ROLINE USB 2.0 Kabel, Micro USB A ST - Micro USB B ST, 1,8m

ROLINE Câble USB 2.0, Micro USB A mâle - Micro USB B mâle, 1,8m

ROLINE USB 2.0 Cable, Micro A - Micro B, M/M, 1.8 m


ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE
△	C	ECR # 091202-2 EDIT PACKING	12/02/09'

MICRO USB A TYPE MALE

INS:WHITE

P1




TUSB-0134

MICRO USB B TYPE MALE

INS:BLACK

P2



TUSB-0137

NOTES:

1. CABLE:

UL-2725 [28AWG(7/0.127 T.C)*1P INS:HD-PE ID:0.8±0.05
+28AWG(7/0.127 T.C)*2C INS:PP ID:0.63±0.05+AL-FOIL/MYLAR
+DRAIN WIRE(7/0.127 T.C)+BRAID 85%] PVC JACKET;
OD:3.0±0.15mm COLOR:BLACK(NK-K01) REV 2.0

2. CONNECTORS:

P1: MICRO USB A TYPE MALE GOLD PLATED 30u" CONTACT,
NICKEL PLATED SHELL REV 2.0

P2: MICRO USB B TYPE MALE GOLD PLATED 30u" CONTACT,
NICKEL PLATED SHELL REV 2.0

3. HOOD: MOLDED TYPE, PVC 45P, COLOR: BLACK(NK-K01)

4. TEST REQUEST:

<1>.100% OPEN SHORT & MIS WIRE TEST.

<2>.CONTACT RESISTANCE 3 Ohm MAX.

<3>.INSULATION RESISTANCE 10M Ohm MIN.

5. PACKING: EACH PC / POLYBAG + SMALL HEADER CARD + BAR CODE LABEL

△ 10 PCS / INNER CTN; 80 PCS / MASTER CTN.

△ 6. BAR CODE NO.: 7611990188260.

PIN OUT

	P1		P2	
RED	1	_____	1	VBUS
WHITE	2	_____	2	D-
GREEN	3	_____	3	D+
	4	_____		
BLACK	5	_____	5	GND

SHELL _____ BRAID _____ SHELL

Tolerance	Inch	M/M
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05

Rotronic co., LTD.

Title
MICRO USB A/M - MICRO USB B/M CABLE

Item No. : 11.02.8753-10

Draw	FANNIE 12/02/09'	App'd	Customer: T-RAG
Chek		Scale	NONE
Engr		Units	m/m
		Third Angle Projection	
	Dwg No. 170-3589	REV:C	Sheet 1/1