


KEMET Part Number: PME261KA5100KR19T0
(P561HE103K220L)

PME261/P561, Film, Metallized Paper, Commercial Grade, 0.01 uF, 10%, 400 V, 85C, Lead Spacing = 10.2mm



General Information

Supplier:	KEMET
Series:	PME261/P561
Dielectric:	Metallized Paper
Style:	Radial
Features:	Pulse in DC and low frequency applications
RoHS:	Yes
Lead:	Wire Leads
Construction:	Molded
Miscellaneous:	AC Operation: 70C MAX

Dimensions

L	13.5mm MAX
H	7.5mm MAX
T	3.9mm MAX
S	10.2mm +0.6/-0.1mm
H0	18.5mm +/-0.5mm
F	0.6mm +/-0.05mm

Packaging Specifications

Packaging:	T&R
Packaging Quantity:	700

Specifications

Capacitance:	0.01 uF
Capacitance Tolerance:	10%
Voltage DC:	400 VDC
Voltage AC:	220 VAC
Temperature Range:	-40/+100C
Rated Temperature:	85C
Dissipation Factor:	1.3% 1kHz
Insulation Resistance:	12 GOhms
Max dVdt:	2,000 V