

**BU-P1081-XX-\***  
(STACKABLE MINI-BANANA TEST LEAD)



- Overmolded, stackable mini (3mm) banana plugs on each end. Banana plugs are gold plated beryllium copper. Wire is 20 AWG with a PVC jacket.
- Ratings: Hands Free testing to 3000VRMS
  - 5 Amps.
- Length: in inches designated by “XX” in the part number:
  - Standard Lengths 12”, 24” & 36”
- Colors: designated by “\*” in the part number: -0 black, -2 red, -4 Yellow
- RoHS Compliant