



# GE Lighting

### Biax Extra Mini™ 15W E27 2700K

**Product code: 10632**

**Description: FLE15TBX/XM/827 E27 220-240V LBX 1/6**

#### Physical Characteristics

Max. Overall Length, (A) :	128 mm
Max Overall Diameter, (B):	42 mm
Max Plastic, Base Height ,(C):	63 mm
Max Glass Length,(D):	65 mm
Base type:	E27
Mass of lamp:	63 g

#### Operating Conditions

Burning position:	any
Luminaire characteristics:	Indoor open/enclosed
Dimmability:	nondimmable

#### Electrical Data

	Nominal	Min.	Max.
Lamp Watts:	15 W		
Lamp Volts:	230 V	220 V	240V
Lamp Amps:			120mA
Input Frequency:	50/60Hz		
THD:			170%


#### Photometric Data

	Nominal	Min.	Max.
Initial Lumens (VBU):	900 Lm		
Initial Lumens (VBD):	765 lm		
Average Lated Life	15,000 Hours		
Number of Starts	30,000 cycles		
Infant mortality within 1000h			1%
Lumen Maintenance @ 2000h		90%	88%
Correlated Colour Temperature (CCT):	2,700 K		
Colour Rendering Index (Ra) CRI:		82	
CIE Chromaticity Coordinates:	X: 0.459 Y: 0.415		
Starting Time			1.5sec
Warm Up Time to 80%:	20 sec		
Operating Temperature Range		10°C	40°C
Starting Temperature Range		-15°C	50°C

#### Others

Standard pack:	6 pcs
Case size (length x height x width):	mm
EAN number:	0043168106320
Mass of single packed lamp:	g
Mass of case:	kg
Pallet quantity:	

#### Outline



#### Note

All performance data shows approximate values based on normal operating conditions with auxiliary equipment that meets current published specifications. Data subjects to change without notice.