



### Specifications of eOne 500

- Microsoft® Windows® 98 Second Edition
- Intel® Celeron™ 500MHz (w/128 KB)
- 64MB SDRAM on board
- 2 USB Ports, Video Input port
- Microphone & Stereo Speakers built-in
- Audio In & Out, Microphone In, 1 Midi/Game
- Works 2000, Netscape® Communicator, eWare
- AOL 3 month membership included, [click here](#) for details
- eMachines Network Internet Service
- 15" SVGA 0.28mm CRT (14" Viewable Size)
- ATI Rage XL 3D 2x AGP with 8MB SDRAM
- Crystal CS4280 PCI Audio
- 24x Max. CD-ROM Drive
- 8.4 GB HDD
- 3.5" 1.44MB FDD
- 56K\* ITU V.90 Fax/Modem
- 10Base-T Ethernet HomePNA 1.0(Intel AnyPoint)
- PS/2 Keyboard, Wheel Mouse; 1 Serial / 1 Parallel

Factory refurbished with a 12 months return-to-base warranty