

Bottle jacks



Built for tough daily use in industrial workshops and garages. A tough cast iron base includes screw in components for easy maintenance. All models include a quality chrome plated ram with additional screw in/out height adjuster. Supplied with two piece pumping handle on 2, 4, 6 and 8 ton models and fold down carry handles on 10, 12 and 20 ton models. Fully tested to European standards and automatic overload protected.

349976

Order code	Model	Capacity (tonne)	Jack height		Weight (kg)	Price each
			Minimum (mm)	Maximum (mm)		
145-5453	CBJ2	2	155	295	3.0	
145-5454	CBJ4	4	190	385	3.8	
145-5455	CBJ6	6	195	405	5.5	
145-5456	CBJ8	8	200	415	6.2	
145-5457	CBJ10	10	200	420	6.9	
145-5458	CBJ12	12	210	435	8.0	
145-5459	CBJ20	20	240	490	14.0	