





PLG4.1.3

PLG54

#### PLG3.2 3.5" 120 WATT TWO-WAY SPEAKERS

- Standard 3.5" Size Fits OEM Locations
- Yellow Color Poly Injected Cone
- Non-Fatiguing Butyl Rubber Surround 0.5" Neodymium Dome Tweeter
- High Temperature Aluminum Voice Coil
- Strong Capacitor for Excellent Performance Yellow Coated Steel Basket
- 20 oz. Magnet Structure Impedance: 4 Ohms
- Rubber Magnet Cover
- Power Handling: 60 Watts RMS /120 Watts Peak
- Frequency Response: 100-20KHz Includes Wires and Installation Hardware
- Mounting Depth: 1.65"

#### PLG4.2 4" 140 WATT TWO-WAY SPEAKERS

- Standard 4" Size Fits OEM Locations
- Yellow Color Poly Injected Cone Non-Fatiguing Butyl Rubber Surround
- 0.5" Neodymium Dome Tweeter
- High Temperature Aluminum Voice Coil
- Strong Capacitor for Excellent Performance
- Yellow Coated Steel Basket 20 oz. Magnet Structure Rubber Magnet Cover
- Power Handling: 70 Watts RMS /140 Watts Peak
- Frequency Response: 90-20KHz

- Impedance: 4 Ohms
- Includes Grills, Wires Installation Hardware Mounting Depth: 1.85"

### **PLG41.3** 4" x 10" 300 WATT THREE-WAY SPEAKERS

- Standard 4"x10" Size Fits OEM Locations
- Yellow Color Poly Injected Cone
- Non-Fatiguing Butyl Rubber Surround 2" Polymer Cone Midrange
- 0.5" Neodymium Dome Tweeter

- High Temperature Aluminum Voice Coil
- Strong Capacitor for Excellent Performance
- Yellow Coated Steel Basket 45 oz. Magnet Rubber Magnet Cover Impedance: 4 Ohms
- Power Handling: 150 Watts RMS /300 Watts Peak
- Frequency Response: 60-22KHzIncludes Grills, Wires and Installation Hardware
- Mounting Depth: 2.45"

### **PLG46.2** 4" x 6" 180 Watt Two-Way Speakers

- Standard 4"x6" Size Fits OEM Locations
- Yellow Color Poly Injected Cone
- Non-Fatiguing Butyl Rubber Surround 0.5" Neodymium Dome Tweeter
- High Temperature Aluminum Voice Coil
- Strong Capacitor for Excellent Performance Yellow Coated Steel Basket - Impedance: 4 Ohms
- 30 oz. Magnet Structure Rubber Magnet Cover
- Power Handling: 90 Watts RMS /180 Watts Peak
- Frequency Response: 70-20KHz Includes Grills, Wires and Installation Hardware
- Mounting Depth: 2"

# **PLG46.3** 4" x 6" 180 Watt Three-Way Speakers

- Standard 4"x6" Size Fits OEM Locations
- Yellow Color Poly Injected Cone Non-Fatiguing Butyl Rubber Surround
- 0.5" Neodymium Dome Midrange

- High Temperature Aluminum Voice Coil
- Strong Capacitor for Excellent Performance Yellow Coated Steel Basket - Impedance: 4 Ohms
- 30 oz. Magnet Structure Rubber Magnet Cover
- Power Handling: 90 Watts RMS /180 Watts Peak
- Frequency Response: 70-20KHz
- Includes Grills, Wires and Installation Hardware Mounting Depth: 2"

- **PLG5.2** 5.25" 140 WATT TWO-WAY SPEAKERS
- Standard 5 25" Size Fits OFM Locations
- Yellow Color Poly Injected Cone
- Non-Fatiguing Butyl Rubber Surround 0.5" Neodymium Dome Tweeter
- High Temperature Aluminum Voice Coil Strong Capacitor for Excellent Performance
- Yellow Coated Steel Basket Impedance: 4 Ohms
- 30 oz. Magnet Structure Rubber Magnet Cover
- Power Handling: 70 Watts RMS /140 Watts Peak
- Frequency Response: 80-20KHz
- Includes Grills, Wires and Installation Hardware
- Mounting Depth: 2"

### PLG5.3 5.25" 140 WATT THREE-WAY SPEAKERS

- Standard 5.25" Size Fits OEM Locations
- Yellow Color Poly Injected Cone
- Non-Fatiguing Butyl Rubber Surround 0.5" Neodymium Dome Midrange
- Super Film Tweeter
- High Temperature Aluminum Voice Coil
- Strong Capacitor for Excellent Performance
- Yellow Coated Steel Basket
- 30 oz Magnet Structure
- Rubber Magnet Cover
- Power Handling: 70 Watts RMS /140 Watts Peak Frequency Response: 80-20KHz
- Impedance: 4 Ohms Includes Custom Grills, Wires and Installation
- Hardware
- Mounting Depth: 2"

# PLG54 5" 200 WATT MID BASS WOOFER

- Yellow CD P.P. Cone
- Specially Treated Rubber Surround
- Edge Suspension

- 1.0" High Temperature Aluminum Voice Coil
- Magnet Weight: 30 Oz
- Impedance: 4 OHM

- 200 Watts Peak Power
- Mounting Depth: 2.20" Cut-out Size: Ф113 mm

For more detailed specifications, product-specific information and models visit www.PyleAudio.com