



TL-300

Test lead set with crocodile clips (red, black, yellow), case, and temperature probe

Technical specifications

Current-carrying capacity	10 A
Current-carrying capacity	10 A
Measurement Category	
Probes	CAT IV/1000 V (with cover) CAT II/1000 V (without cover)
Crocodile clips	CAT IV/600 V, CAT III/1000 V
Pollution degree	2
Safety cert.:	DIN VDE 0411/EN 61010/IEC 61010
Temperature probes	K-type flexible wire probe 4 mm plug (distance 19 mm)
Probe length	approx. 0.9 m
Temperature range	-20 °C...+250 °C
Accuracy	-20...0 °C: ± 2.5 °C or $\pm 1.5\%$ rdg. 0...250 °C: ± 1.1 °C or $\pm 0.4\%$ rdg.

PVC

K
Typ

4
mm



CAT III
1000 V

CAT IV
600 V

10 A