

Side panel - UCS SW 125-H 9005 - 2203369

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Side panel for use with housing half shells 125 x 87 mm and 145 x 125 mm in size; panel thickness: 2 mm; total height of housing: 67 mm; material: polycarbonate; color: black similar to RAL 9005

Key Commercial Data

Packing unit	10 STK
GTIN	
GTIN	4055626427393
Weight per Piece (excluding packing)	13.610 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

General

Housing material	PC
------------------	----

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 100 °C (depending on power dissipation)

Dimensions

Width	96 mm
Height	59.5 mm
Depth	2 mm

Classifications

eCl@ss

eCl@ss 5.1	27180506
------------	----------

Side panel - UCS SW 125-H 9005 - 2203369

Classifications

eCl@ss

eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031