

EPIC® MH Coax 1.6mm

The mixed assembly guarantees high flexibility. For applications in mechanical and plant engineering, for printing machines and slide-in technology.



Interference signals



Wind Energy



Rail



Mechanical and plant engineering



Automation & fältinstallation

EPIC® MH Coax 1.6mm

Technical Data

Classification:	ETIM 5.0 Class-ID: EC002641 ETIM 5.0 Class-Description: Modular connector (industrial connector)
Rated voltage (V):	50
Rated impulse voltage:	0,8 kV
Rated current (A):	16
Pollution degree:	3
Flammability:	UL94 V-0
Number of contacts:	1
Cycle of mechanical operation:	500
Certifications:	UL-tested: UL File Number: E75770
Temperature range:	-40°C ... +125°C

Note

Photographs are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.



EPIC® MH Coax 1.6mm

Article number	Article description	Contact type	Number of operating contacts
44423260	EPIC® MHS Coax D=1.6mm	male	1
44423261	EPIC® MHB Coax D=1.6mm	female	1

Last Update (24.09.2017)

©2017 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16