

# HL 1920 E

**NEW!**

Available October 2016

## Technical Specifications

Voltage:	120 VAC / 60Hz
Output:	1500 watts
Amps:	12.5
Temperature:	120 – 1100 °F (50 – 600 °C)
Airflow rate:	4 / 4-8 / 6-13 cfm.
Stages:	3
Highlights:	Higher durability (+20 %), optimized weight balance, hanging ring, optional temperature scanner and fine dust filter
Power cord:	Industrial grade rubber, length: 6ft
Motor:	Brush motor
Heating element:	Ceramic heating element
Motor lifetime:	600h
Accessories:	Use of our standard accessories
Dimensions:	9.96" x 3.33" x 7.87" (l x w x h)
Net Weight:	1.9 lbs (30.37 oz)
Single Sell Pack:	Dimensions: 10.20" x 3.54" x 9.33" Weight: 2.31 lbs (36.93 oz)
Country of origin:	Romania
Warranty:	One year limited



UPC-Code

018139375302

Prod. No.

110025596



RoHS  
Compliant



double insulated

**ISO**  
9001:  
2015  
14001:  
2015