









\*2.50±0.20 FOR APPLICATION MACHINE STRIPPER CRIMPER DX 271 ONLY.



DUBOX HOUSING; SINGLE ROW  
P/N 65240-XXX

DUBOX TERMINAL  
LOOSE PIECE 76357-XOY  
ON STRIP 76347-XOY



WIRE SIZE AWG	CRIMP HEIGHT STRANDED WIRE		BELL-MOUTH
	MACHINE	HAND TOOL	
30	0.66±0.04	0.63-0.7	0.20±0.05
28	0.66±0.04		
26	0.69±0.04	0.83-0.89	+0.1
24	0.84±0.04		0.2-0.05
22	0.87±0.04		0.15±0.10

mat'l code		tolerances unless otherwise specified		CUSTOMER COPY		FCCI ELECTRONICS	
lit	REV no	dr	date	projection	title		
F	30885	PNZ	00.10.08	Linear	DUBOX CTW		
C	FD0188	DLE	00.03.20	angles	APPLICATION DATA		
		dr	D LEGRAND	00.03.20	product family	DUBOX	code
		engr	P NIZZI	00.03.20	size	A2	213
		ctr	JF NOTTEAU	00.03.20	scale	N/A	sheet
		appo	PNZ	00.03.20			1 of 1
sheet	revision						
index	sheet						