




Product information Tofino Xenon - TofinoXe-0200T1T1SDDY90007

| Industrial Ethernet:Industrial Firewall System:TOFINO XENON:Tofino Xenon | |
|---|--|
| https://www.e-catalog.beldensolutions.com:443/link/57078-24455-49853-411807-411957/en/TofinoXe-0200T1T1SDDY90007/ui/state | |
| Name | Tofino Xenon |
| |  |
| | Industrial firewall with Stateful Packet Inspection (SPI) and optional Deep Packet Inspection (DPI), transparent layer two operation, DIN rail mounted, fanless design, 2 x 10/100 Mbit/s Ethernet Ports |
| Delivery informations | |
| Availability | available |
| Product description | |
| Description | Industrial firewall with Stateful Packet Inspection (SPI) and optional Deep Packet Inspection (DPI), transparent layer two operation, DIN rail mounted, fanless design, 2 x 10/100 Mbit/s Ethernet Ports |
| Port type and quantity | 2 x 10/100 Mbit/s Ethernet Ports |
| Type | TofinoXe-0200T1T1SDDY90007 |
| Order No. | TofinoXe-0200T1T1SDDY90007 |
| Classification | |
| Belden brand | Hirschmann |
| More Interfaces | |
| Power supply/signaling contact | 1 x plug-in terminal block, 6-pin |
| Digital Input | 1 x plug-in terminal block, 2-pin |
| V.24 interface | 1 x RJ11 socket |
| USB interface | 1 x USB to connect the AutoConfiguration Adapter ACA21-USB |
| Network size - length of cable | |
| Twisted pair (TP) | 0 m ... 100 m |
| Network size - cascability | |
| Line - / star topology | any |
| Power requirements | |
| Operating voltage | 12/24/48 V DC/24V AC (redundant) |
| Power consumption | 5 W |
| Ambient conditions | |
| Operating temperature | 0 °C ... 60 °C |
| Storage/transport temperature | -40 °C ... 70 °C |
| Relative humidity (non-condensing) | 10 % ... 95 % |
| Mechanical construction | |
| Dimensions (W x H x D) | 60 mm x 145 mm x 125 mm |
| Mounting | DIN Rail |
| Weight | 660 g |
| Protection class | IP20 |
| Approvals | |
| Basis Standard | CE, FCC, C-Tick, EN61131, EN 60950 |
| Safety of industrial control equipment | cUL 508 |
| Scope of delivery and accessories | |
| Scope of delivery | Device, terminal blocks, operating instructions, manual on CD |
| Accessories to order separately | Rail power supply RPS 30, RPS 80 EEC, RPS 120 EEC, Tofino Configurator software, ACA21-USB EEC, 19" installation frame, Tofino Firewall LSM, Tofino Modbus TCP Enforcer LSM, Tofino OPC Classic Enforcer LSM, Tofino NetConnect LSM, Tofino EtherNet/IP Enforcer LSM |



HIRSCHMANN

A **BELDEN** BRAND

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.