



Specifications:

1. Circuit board material: FR4 (UL94 V-0).
2. Closed-back carrier is designed for mounting on 35mm DIN rail.
3. Maximum load: 15 Amps, 125VAC.
4. Terminals: WAGO series 256, color-coded, accept one #28-12 AWG wire per segment.
5. For use in pollution degree 2 environments, up to 45°C (113°F) ambient, non-condensing
6. RoHS compliant construction.



CUSTOMER SIGNOFF: \_\_\_\_\_  
 DATE: \_\_\_\_\_

**AC UTILITY RECEPTACLE, WITH  
 CLOSED-BOTTOM  
 35mm DIN RAIL CARRIER**

3	09/09/08	Add note 6 - RoHS	N/A	JCK
2	08/01/08	Add UL logo; note 5 was 6	N/A	JCK
1	03/12/08	Add note 6	N/A	JCK
REV.	DATE	DESCRIPTION	DCO	BY



N120 W19129 Freistadt Road  
 P.O. Box 1015  
 Germantown, WI 53022

File Name  
 PRO1236-31-1.dwg

Title/ Ident No.	PROPOSAL 1236	Page 1 of 1
Scale	Date Drawn	Drawn By
NTS	02/23/06	JCK
		App. By

Copyright © WAGO Corp. all rights reserved. This document contains information that is proprietary to WAGO Corporation and is delivered to others on the express condition that neither it nor the information it contains will be used, disclosed, reproduced, stored or transmitted in whole or in part without the prior written consent of WAGO Corporation.

Custom P/N: 51015188

File: