



4G LTE Mobile Wi-Fi

Go Anywhere
Connect Everywhere

M7200



4G 4G LTE
150Mbps

8h 8hrs Usage

M tpMiFi
App

Highlights

Share 4G LTE Connection on the Go

The M7200 features a compact, elegant design very suitable for travel, business trips, outdoor activities or wherever you may be.



Easy Management with the tpMiFi App

With the tpMiFi App, you can easily access and manage the M7200 from your connected iOS/Android devices. The tpMiFi app allows you to establish data limits, control which devices can access your Wi-Fi, and send messages.



Features



Lightning 4G LTE

- Lightning generation 4G LTE – Supports 4G LTE network, compatible with 3G network
- The Faster Connections – Reaches up to 150Mbps download speed and 50Mbps upload speed, to enjoy HD movies without interruption, download files in seconds, and hold a video chat without dropouts



Convenient Hotspot

- Plug and Play – Just insert a SIM card and power on to create a stable Wi-Fi hotspot to share on the move
- High-Speed Hotspot – Share 2.4GHz Wi-Fi at speed of 300Mbps with up to 10 Wi-Fi devices



8 Hours Usage

- 2000mAh – 2000mAh rechargeable battery capacity
 - 8 hours – 8 hours of 4G sharing
 - 480 hours – 480 hours of standby
- * Actual battery time may vary due to different user environments

Specifications

Hardware

- Interface: 1 micro USB port, 1 SIM card slot
- Button: Power Button, Reset Button
- LED: Wi-Fi LED, Internet LED, Battery LED
- External Power Supply: 5V/1A
- Dimensions (W x D x H): 3.7 × 2.2 × 0.8 in. (94 × 56.7 × 19.8mm)
- Antenna: Internal Antennas

Wireless

- Network Type:
 - 4G: FDD-LTE: B1/B3/B7/B8/B20 (2100/1800/2600/900/800MHz)
 - TDD-LTE: B38/B40/B41 (2600/2300/2500MHz)
 - 3G: DC-HSPA+/HSPA/UMTS: B1/B8(2100/900MHz)
- Wireless Standards: IEEE 802.11b/g/n 2.4GHz
- Frequency: 2.4GHz
- Wireless Speed: 300Mbps
- Transmit Power: <20dBm
- Reception Sensitivity: 11b 11Mbps: -87.5dBm;
 - 11g 54Mbps: -74dBm;
 - 11n HT20 MCS7: -70dBm;
 - 11n HT40 MCS7: -68dBm;
- Wireless Security: Support WPA-PSK/WPA2-PSK,Wireless MAC Filtering, Enable/Disable SSID Broadcast
- DHCP: Server, Client, DHCP Client List

Others

- Certification: CE, RoHS
- System Requirements:
 - Windows 10/8/7/Vista/XP, Mac OS, Android, iOS, Windows Phone
- Environment
 - Operating Temperature: 0℃~40℃ (32°F ~104°F)
 - Storage Temperature: -40℃~70℃ (-40°F ~158°F)
 - Operating Humidity: 10%~90% non-condensing
 - Storage Humidity: 5%~90% non-condensing
- Package Contents
 - Mobile Wi-Fi M7200
 - Micro USB Cable
 - 2000mAh Battery
 - Quick Installation Guide



For more information, please visit
<http://www.tp-link.com/en/products/details/M7200.html>
or scan the QR code left

Specifications are subject to change without notice. TP-Link is a registered trademark of TP-Link Technologies Co., Ltd. Other brands and product names are trademarks or registered trademarks of their respective holders. Copyright ©2017 TP-Link Technologies Co., Ltd. All rights reserved.