



LOWEST PRICE GUARANTEED!

3 BASKET POSITIONS FOR FLEXIBLE STORAGE



Angle Down
Flows parts to front provides maximum accessibility



Flat
Provides maximum space efficiency



Angled Up
Provides maximum bin capacity

Wire Basket Units

Basket units allow high visibility and air circulation. The basket acts as a dispensing and storage module which can be added to 18", 21" and 24" deep shelving units. The collar hook allows the basket to be removed or adjusted to accommodate various product mix and sizes. Baskets are adjustable on 1" increments. 110 lb. load capacity per basket. Adjustable baskets used in combination with shelves are an excellent method to store all types of products. Units can be stationary or mobile. Casters add flexibility and convert stationary units into transport systems. Ideal for exchange charts and par level storage. *(Dividers sold separately)* **Finish:** Chrome



M1836BC6C
(Dividers sold separately)



1836BC6C
(Dividers sold separately)



COLLAR HOOKS
Hooks onto basket corner allowing basket to securely hang.

Mobile Wire Basket Units

Each mobile unit consists of:

- 4 - 63"H posts
- 3 - 9"H adjustable baskets including collar hooks
- 2 - wire shelves
- 4 - donut bumpers
- 4 - swivel 5" x 1-1/4" polyurethane casters, 2 with brakes

| STATIONARY MODEL NO. | DIMENSIONS W" x L" x H" | NO. OF SHELVES | NO. OF BASKETS | SHIP WGT |
|----------------------|-------------------------|----------------|----------------|----------|
| M1836BC6C | 18" x 36" x 69" | 2 | 3 | 78 lbs |
| M1848BC6C | 18" x 48" x 69" | 2 | 3 | 90 lbs |
| M2436BC6C | 24" x 36" x 69" | 2 | 3 | 93 lbs |
| M2448BC6C | 24" x 48" x 69" | 2 | 3 | 108 lbs |

COMPLETE PACKAGES WITH BASKETS

Stationary Wire Basket Units

Each stationary unit consists of:

- 4 - 63"H posts
- 3 - 9"H adjustable baskets including collar hooks
- 2 - wire shelves

| STATIONARY MODEL NO. | DIMENSIONS W" x L" x H" | NO. OF SHELVES | NO. OF BASKETS | SHIP WGT |
|----------------------|-------------------------|----------------|----------------|----------|
| 1836BC6C | 18" x 36" x 63" | 2 | 3 | 70 lbs |
| 1848BC6C | 18" x 48" x 63" | 2 | 3 | 82 lbs |
| 2436BC6C | 24" x 36" x 63" | 2 | 3 | 85 lbs |
| 2448BC6C | 24" x 48" x 63" | 2 | 3 | 100 lbs |