3 Sided Frame

Finish: 304 Stainless Steel

DIMENSIONS

24" x 36"

24" x 48"

24" x 60"

STAINLESS

2436FS

2448FS

2460FS

MODEL NO

SHIP WGT

8 lbs

9 lbs

10 lbs











Open Surgical Case Carts

Corrosion-free surgical case cart transports and delivers surgical instrumentation packs from the OR supply center to the operating room. Finish: 304 Stainless Steel

Each unit consists of:

- 4 42" stainless steel posts
- 2 stainless steel wire shelves
- 1 stainless steel solid shelf
- 1 stainless steel 3-sided frame
- 1 stainless steel push handle
- 4 5" swivel, stainless steel poly stem casters and 2 with brake (casters come with Zerk grease fittings)
- 4 donut bumpers

	DIMENSIONS	NO. OF	SHIP
MODEL NO.	W" x L" x H"	SHELVES	WGT
WRSC3-42-2436FS	24" x 36" x 48"	3	77 lbs
WRSC3-42-2448FS	24" x 48" x 48"	3	88 lbs
WRSC3-42-2460FS	24" x 60" x 48"	3	106 lbs

Each unit consists of:

- 4 54" stainless steel posts
- 3 stainless steel wire shelves
- 1 stainless steel solid shelf
- 1 stainless steel 3-sided frame
- 1 stainless steel push handle
- 4 5" swivel, stainless steel poly stem casters and 2 with brake (casters come with Zerk grease fittings)
- 4 donut bumpers

MODEL NO.	DIMENSIONS W" x L" x H"	NO. OF SHELVES	SHIP WGT
WRSC4-54-2436FS	24" x 36" x 60"	4	94 lbs
WRSC4-54-2448FS	24" x 48" x 60"	4	108 lbs
WRSC4-54-2460FS	24" x 60" x 60"	4	131 lbs

Stainless Steel Work Table with Adjustable Undershelf



Heavy-duty 304 stainless steel processing tables are ideal for pack and prep in sterile environments. Units consist of a flat top work surface with hemmed edges and the lower flat bottom shelf is adjustable from 3" to 27" high. Tables are NSF approved. The support legs are 1-5/8" diameter with a leveling foot which can be converted to a mobile unit with a 3" conductive caster kit, all swivel and 2 with brake. (Sold separately) Finish: 304 Stainless Steel

MODEL NO.	DIMENSIONS W" x L" x H"	NO. OF SHELVES	SHIP WGT
	Stationary Instrument	Table with Shelf	
SST-2436U	24" x 36" x 34"	1	50 lbs
SST-2448U	24" x 48" x 34"	1	60 lbs
SST-2460U	24" x 60" x 34"	1	70 lbs
SST-2472U	24" x 72" x 34"	1	80 lbs
	Mobile K	lit	
SST-MOB	4 Swivel Casters, 2 with Brakes		4 lbs