

RSO1207-5


RSO1215-5

RSO1215-7



Heavy-duty, straight wall containers maximize your space when used for shipping, storage or work-in progress. Greater strength and durability provided by reinforced corners allowing this strong container to hold the heaviest of parts. Containers are injection molded from high-density polyethylene. Straight wall design allows for modular stacking of all sizes on standard pallets. Hand grips on two sides make the container easy to handle and carry. Up to 150 lb. stack capacity.

Available in: Gray									
MODEL NO.	OUTSIDE DIMENSIONS L" x W" x H"	INSIDE DIMENSIONS L" x W" x H"	CTN QTY	VOLUME (CU FT)	SHIP WGT	LID			
RSO1207-5	12" x 7-1/2" x 5"	9-3/4" x 5-1/2" x 5"	1	0.1	2 lbs	-			
RSO1215-5	12" x 15" x 5"	9-1/2" x 13" x 5"	1	0.3	2 lbs	LID1215			
RSO1215-7	12"x 15" x 7-1/2"	9-1/2"x 13" x 7"	1	0.5	3 lbs	LID1215			
RSO1408-7	13-7/8" x 7-3/8" x 6-5/8"	11-3/16" x 5-5/8" x 5-3/4"	1	0.2	2 lbs	-			
RSO2415-5	24" x 15" x 5"	21-1/2" x 13" x 5"	1	0.7	4 lbs	LID2415			
RSO2415-7	24" x 15" x 7-1/2"	21-1/2" x 13" x 7"	1	1.1	5 lbs	LID2415			
RSO2415-9	24" x 15" x 9-1/2"	21-1/2" x 13" x 9"	1	1.4	5 lbs	LID2415			
RSO2422-11*	24" x 22-1/2" x 11"	21-1/2" x 20-1/2" x 10-1/4"	1	3.5	8 lbs	-			



Reinforced external ribbing and stacking rims provide maximum stacking strength up to 150 lbs.

available in Black only and with an attached lid.

RSO2415-5

RSO2415-7

RSO2415-9

RSO2422-11

Straight Wall container shown with optional lid LID2415 (Sold Separately)



AL-35 package of 24

DLY-2415 is 24"L x 15"W with 1" Ledge, available in Black. **DLY-3018** is 30"L x 18"W with Padded Rubber Trim, available in Blue. Both dollies have 1,000 lb. load capacity.

MODEL NO.	DESCRIPTION	CTN WGT
DLY-2415	Dolly with 1" Ledge	14 lbs
DLY-3018	Dolly with Padded Rubber Trim	19 lbs
Bins sold separately.		

YOUR BINS

DIY-2415

Interior Dimensions 24"L x 15"W Exterior Dimensions 28"L x 18-1/2"W

Strong, reliable and reusable Collapsable Containers offer "true form" ergonomic carrying handles, designed for safer lifting. Containers have knock down ratios as high as 5:1, saving space and return freight. Modular to standard AIAG 48" x 45" pallet footprint. Large label and cardholder area provide easy identification and improved inventory control.

Available in: Gray

MODEL NO.	OUTSIDE DIMENSIONS L" x W" x H"	INSIDE DIMENSIONS L" x W" x H"	CTN QTY	SHIP WGT
RC1215-089	12" x 15" x 9"	10-1/2" x 13-3/8" x 8-1/2"	1	4 lbs
RC2415-075	24" x 15" x 7-1/2"	22-1/2" x 13-5/8" x 7"	1	5 lbs
RC2415-089	24" x 15" x 9"	22-1/4" x 13-3/4" x 8-1/2"	1	5 lbs
RC2415-111	24" x 15" x 11"	22-1/2" x 13-1/2" x 10-3/4"	1	6 lbs

SPACE SAVING, RETURNABLE,

