

## PNOZ m EF 8DI4DO

772142



Configurable control system PNOZmulti 2 expansion module 8 safe digital inputs, 4 safe semiconductor outputs.

### Technical details

Approvals:	CE;cULus Listed;TÜV;BG
Number of digital inputs:	8
Positive switching 1-pole SC output:	4
Supply voltage 2 (V):	24
Supply voltage type 2:	DC
Terminal style:	Plug-in
Version for extreme environ. conditions:	Standard
Width dimension:	22.5 mm
Height dimension:	101.4 mm
Depth dimension:	120.0 mm
Gross weight:	115 g
Net weight:	105 g
Ambient temperature:	0 - 60 °C

### Accessories



750004

PNOZ s Setscrew terminals 22,5mm



751004

PNOZ s Setspring loaded terminals 22,5mm

## Optional accessories



779260

PNOZ mm0.xp connector left (10 pcs)

---