



**SRT5KTF**

★★★★★  
Be the first to [write a review](#)

Share this Product: [f](#) [g+](#) [t](#) [p](#)

**RoHS**  
Includes : User Manual

- Product Overview
- Technical Specifications**
- Documentation
- Drawings
- Options
- Ratings & Reviews

**Output** Print Technical Specification

Nominal Output Voltage	120V , 208V
Other Output Voltages	240
Always on Outlets	12
Maximum Total Current Draw	5000
Output Connections	
(8) NEMA 5-20R (Battery Backup)	
(1) NEMA L6-30R (Battery Backup)	
(1) NEMA L14-30R (Battery Backup)	
(2) NEMA L6-20R (Battery Backup)	

**Input**

Nominal Input Voltage	208V , 240V
Input frequency	50/60 Hz
Input Connections	NEMA L6-30P
Cord Length	3ft ( 0.91meters )
Number of Power Cords	1

**Physical**

Maximum Height	17.0inches ( 432mm , 43.2CM )
Maximum Width	5.1inches ( 130mm , 13.0CM )
Maximum Depth	26.0inches ( 660mm , 66.0CM )
Net Weight	125.0lbs. ( 56.7KG )
Shipping weight	140.0lbs. ( 63.5KG )
Shipping Height	13.68inches ( 347mm , 34.7CM )
Shipping Width	23.74inches ( 603mm , 60.3CM )
Shipping Depth	38.6inches ( 980mm , 98.0CM )
Color	Black
Units per Pallet	6.0

**Environmental**

Operating Temperature	32 - 104 °F ( 0 - 40 °C )
Operating Relative Humidity	0 - 95% no %
Operating Elevation	0-10000ft ( 0-3000meters )
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95% no %
Storage Elevation	0-50000ft ( 0-15000meters )

**Conformance**

Standard warranty	2 years repair or replace
-------------------	---------------------------

**Sustainable Offer Status**

RoHS	Compliant
REACH	REACH: Contains No SVHCs
EOL	Available in Documentation tab

---

WHO WE ARE

[APC History](#)  
[Investor Relations](#)  
[Careers](#)  
[Sustainability](#)

CONNECT WITH US

[Press](#)  
[APC Blog](#)  
[Schneider Electric TV](#)  
[Schneider Electric Data Center Blog](#)  
[Contact Us](#)  
[Rate this website](#)

FIND A RESELLER

Zip/Postal Code

CATALOG KEYCODE

Enter Key Code

---

[TERMS & CONDITIONS](#) | [PRIVACY STATEMENT](#)

© 2018, APC by Schneider Electric

