

Universe	Professional
Type	Lighting
Category	ATEX / HAZLOC headlamps
Subcategory	ATEX headlamps



PIXA® 3 (ATEX)


The PIXA 3 headlamp is rugged and versatile. The multi-beam adapts to all situations: close-range work, movement, and long-range vision. CONSTANT LIGHTING technology: brightness does not decrease gradually as the batteries are drained. It meets ATEX zone 2/22 certification requirements for work in explosive environments.



Multi-beam: multiple lighting modes available for close-range work, for movement or for long-range vision.



Knob can be handled with gloves to facilitate use of the headlamp under any conditions.



Headlamp meeting ATEX zone 2/22 certification requirements for work in explosive environments.



Excellent resistance to falls, to impacts and to crushing.

Short Description

Headlamp for use in ATEX zone 2/22 explosive environments, suitable for proximity lighting, movement and long-range vision. 100 lumens

Selling Points

- Headlamp keeps hands free for work and can be:
 - worn on the head with the headband
 - attached to the helmet with a mounting plate (included)
 - placed on the ground
- CONSTANT LIGHTING technology ensures brightness that does not gradually decrease as the battery drains
- Several lighting modes adapt to each situation:
 - a mode adapted for close-range work: uniform flood beam
 - a mode adapted for movement: mixed beam with focused component allows user to move around comfortably
 - a mode adapted for long-range vision: focused beam
- Lighting for professionals that is reliable, practical and durable:
 - automatically switches to reserve mode when batteries are almost drained (signaled by blinking light and red indicator)
 - rotating knob that is ergonomic, even with gloves
 - storage position helps protect the headlamp lens and prevents inadvertently turning it on
 - may be used in explosive environments
 - excellent resistance to falls (2 m), impacts, and crushing (80 kg)
 - comfortable and washable elastic headband
 - resistant to chemicals
- ATEX zone 2/22 certified headlamp

Specification

- Weight: 160g
 - Technology: CONSTANT LIGHTING
 - Beam pattern: flood, mixed or focused
 - Energy: 2 AA/LR06 batteries (included)
 - Battery compatibility: rechargeable Ni-MH and lithium
 - Watertightness: IP 67 (waterproof to -1 meter for 30 minutes; no maintenance required after immersion)
-

Lighting performance

Lighting technology	Lighting modes	Beam pattern	Brightness	Distance	Burn time	Reserve mode
CONSTANT LIGHTING	close-range work	flood	20 lm	15 m	26 h	10 lm for 13 h
	movement	mixed	60 lm	45 m	6h30	
	distance vision	focused	100 lm	90 m	3h30	

Specifications by reference

Reference(s)	E78CHB 2
	Certification(s) : CE, II 3 G Ex nA ic IIB T4 Gc, II 3 D Ex tc IIIB or IIIC T135° C Dc, room temperature: -30° C to +40° C
Color(s)	black/yellow
Made in	MY
Guarantee	3 years
Packing	1
Case quantity	36
EAN	3342540098497

Accessory(ies) POCHE PIXA
RUBBER
PIXA headband
PIXADAPT

Related product(s) VERTEX® BEST
ALVEO VENT
PIXA® 3 (HAZLOC)