

Universe	Sport
Type	Lighting
Category	CLASSIC headlamps
Subcategory	CLASSIC headlamps



Hybrid
CONCEPT

TIKKA®

Simple and compact, the TIKKA headlamp offers 200 lumen brightness and a wide beam. With its long burn time, it is practical for outdoor activities like camping or trekking, or for traveling, and also for daily activities and projects around the house. The phosphorescent reflector helps you find it in the dark, and the red lighting prevents members of a group from blinding each other. TIKKA is a HYBRID headlamp that is also compatible with the CORE rechargeable battery.



Wide, uniform beam for comfortable close-range vision. White and red lighting for nocturnal stealth.



Compact headlamp.



Adjustable elastic headband with emergency whistle.



TIKKA is a HYBRID headlamp: it comes with three standard batteries, and is also compatible with the CORE rechargeable battery.

Short Description Compact headlamp for proximity lighting and some movement. 200 lumens

- Selling Points**
- Compact and lightweight: only 86 g
 - Long burn time
 - Simple to use, thanks to its single button with which to quickly and easily select the lighting mode
 - Three lighting modes: proximity, movement and distance vision
 - Red lighting preserves night vision and stealth, and prevents members of a group from blinding each other
 - Phosphorescent reflector is useful for locating the lamp in the dark
 - TIKKA is a HYBRID headlamp: it comes with three standard batteries, and is also compatible with the CORE rechargeable battery
-

- Specification**
- Light output: 200 lumens
 - Weight: 86g
 - Beam pattern: wide
 - Energy: Three AAA/LR03 batteries (included) or CORE rechargeable battery (available as accessory)
 - Battery compatibility: rechargeable Ni-MH
 - Certification(s): CE
 - Watertightness: IP X4 (weather resistant)
-

Lighting performance

Lighting color	Lighting modes	Brightness	Distance	Burn time
white	MAX AUTONOMY	5 lm	10 m	240 h
	STANDARD	100 lm	40 m	60 h
	MAX POWER	200 lm	60 m	
red	proximity	2 lm	5 m	visible at 700 m for 400 h
	strobe			

Specifications by reference

Reference(s)	E93AAA	E93AAB	E93AAC	E93AAD
				
Color(s)	black	green	red	blue
Made in	MY	MY	MY	MY
Guarantee	5 years	5 years	5 years	5 years
Packing	1	1	1	1
Case quantity	50	50	50	50
EAN	3342540106727	3342540106710	3342540106697	3342540106703

Accessory(ies)

CORE
KIT ADAPT
NOCTILIGHT
POCHE