

Product information

18V Router/Trimmer BL LXT



DRT50ZJX3

Battery Type	Lithium-ion
Body only machine	1
Voltage	18 v
Collet Capacity	3/8" and 1/4"
Noise sound pressure	78 dB(A)
Noise K factor	3 dB(A)
Plunge Capacity (Trimmer)	0 - 40 mm
Plunge Capacity (Plunge)	0 - 35 mm
No Load Speed	10,000 - 30,000 rpm
Vibration K factor	1.5 m/sec ²
Vibration: Cutting MDF	4.5 m/sec ²
Vibration no load	2.5 m/sec ²
Net weight	2.1 kg



STANDARD EQUIPMENT: 821552-6 MAKPAC CONNECTOR CASE (TYPE 4), Trimmer guide, Trimmer base, Plunge base, Straight guide, Tilt base, Dust nozzle for trimmer base, Hex wrench x2, Offset base, Dust nozzle for plunge base, Collet cone, Template guide for trimmer, Grip 36, Template guide for plunge base, Grip attachment, Guide holder

- Brushless motor
- Soft start
- Variable speed control dial.
- Constant speed control
- LED job light
- Push button with lock on/off
- Connectable to dust extractor
- Aluminium base for higher durability and accuracy
- Aluminium housing
- Shaft lock

Details correct as of: 9-1-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makitauk.com